

**N.G.O. di Reggio Calabria - Lista cavi  
MEDIA INTEGRAZIONE**

	CHK	Descrizione Linea	Modello Cavo	Partenza	Destinazione	Mt.
1	<input type="checkbox"/>	Y - Surgical Camera Out	Sommer - 600-0051L	Rack	Boom arms xx	29,50
2	<input type="checkbox"/>	C - Surgical Camera Out	Sommer - 600-0051L	Rack	Boom arms xx	29,50
3	<input type="checkbox"/>	Y - Twin Monitor 1 In	Sommer - 600-0051L	Rack	Boom arms xx	29,50
4	<input type="checkbox"/>	C - Twin Monitor 1 In	Sommer - 600-0051L	Rack	Boom arms xx	29,50
5	<input type="checkbox"/>	Y - Single Screen In	Sommer - 600-0051L	Rack	Boom arms xx	29,50
6	<input type="checkbox"/>	C - Single Screen In	Sommer - 600-0051L	Rack	Boom arms xx	29,50
7	<input type="checkbox"/>	Spare 1 - W25	Sommer - 600-0051L	Rack	Boom arms xx	29,50
8	<input type="checkbox"/>	Spare 2 - W25	Sommer - 600-0051L	Rack	Boom arms xx	29,50
9	<input type="checkbox"/>	RS232 - Touchscreen Area Sterile	Percon - FTP FLEX CAT5 300MHZ	Rack	Boom arms xx	29,50
10	<input type="checkbox"/>	TP - Extender Vga In - Touchscreen area st	Percon - FTP FLEX CAT5 300MHZ	Rack	Boom arms xx	29,50
11	<input type="checkbox"/>	Spare 1 - W22	Percon - FTP FLEX CAT5 300MHZ	Rack	Boom arms xx	29,50
12	<input type="checkbox"/>	Spare 2 - W22	Percon - FTP FLEX CAT5 300MHZ	Rack	Boom arms xx	29,50
13	<input type="checkbox"/>	Alim - Touchsreen Area Sterile	Sommer - 700-0101-0315	Rack	Boom arms xx	29,50
14	<input type="checkbox"/>	Trasporto CAT5	Percon - FTP FLEX CAT5 300MHZ	Rack	Plasma panel - TFT	20,50
15	<input type="checkbox"/>	Trasporto CAT5	Percon - FTP FLEX CAT5 300MHZ	Rack	Plasma panel - TFT	20,50
16	<input type="checkbox"/>	Spare 1 - W22	Percon - FTP FLEX CAT5 300MHZ	Rack	Plasma panel - TFT	20,50
17	<input type="checkbox"/>	Spare 2 - W22	Percon - FTP FLEX CAT5 300MHZ	Rack	Plasma panel - TFT	20,50
18	<input type="checkbox"/>	Y - TFT 40" In	Sommer - 600-0051L	Rack	Plasma panel - TFT	20,50
19	<input type="checkbox"/>	C - TFT 40" In	Sommer - 600-0051L	Rack	Plasma panel - TFT	20,50
20	<input type="checkbox"/>	Spare 1 - W25	Sommer - 600-0051L	Rack	Plasma panel - TFT	20,50
21	<input type="checkbox"/>	Spare 2 - W25	Sommer - 600-0051L	Rack	Plasma panel - TFT	20,50
22	<input type="checkbox"/>	SPK - Speaker 1	Sommer - MERIDIAN SP240	Rack	Speaker	23,50
23	<input type="checkbox"/>	SPK - Speaker 2	Sommer - MERIDIAN SP240	Rack	Speaker	17,50
24	<input type="checkbox"/>	SPK - Speaker 3	Sommer - MERIDIAN SP240	Rack	Speaker	23,00
25	<input type="checkbox"/>	SPK - Speaker 4	Sommer - MERIDIAN SP240	Rack	Speaker	18,00
26	<input type="checkbox"/>	Spare 1 - W24	Sommer - MERIDIAN SP240	Rack	Speaker	23,50
27	<input type="checkbox"/>	Spare 2 - W24	Sommer - MERIDIAN SP240	Rack	Speaker	17,50
28	<input type="checkbox"/>	AUDIO - Patch Panel Out	Sommer - 200-0401	Rack	Technical panel Touchscreen	28,30
29	<input type="checkbox"/>	AUDIO - Patch Panel In	Sommer - 200-0401	Rack	Technical panel Touchscreen	28,30
30	<input type="checkbox"/>	Spare 1 - W23	Sommer - 200-0401	Rack	Technical panel Touchscreen	28,30
31	<input type="checkbox"/>	Spare 2 - W23	Sommer - 200-0401	Rack	Technical panel Touchscreen	28,30
32	<input type="checkbox"/>	RS232 - Touchscreen Panel	Percon - FTP FLEX CAT5 300MHZ	Rack	Technical panel Touchscreen	28,30
33	<input type="checkbox"/>	TP - Extender Mouse-keyb In	Percon - FTP FLEX CAT5 300MHZ	Rack	Technical panel Touchscreen	28,30
34	<input type="checkbox"/>	TP - Extender Vga In - Touchscreen Panel	Percon - FTP FLEX CAT5 300MHZ	Rack	Technical panel Touchscreen	28,30

**N.G.O. di Reggio Calabria - Lista cavi  
MEDIA INTEGRAZIONE**

	CHK	Descrizione Linea	Modello Cavo	Partenza	Destinazione	Mt.
35	<input type="checkbox"/>	Spare 1 - W22	Percon - FTP FLEX CAT5 300MHZ	Rack	Technical panel Touchscreen	28,30
36	<input type="checkbox"/>	Spare 2 - W22	Percon - FTP FLEX CAT5 300MHZ	Rack	Technical panel Touchscreen	28,30
37	<input type="checkbox"/>	CV - Patch Panel	Sommer - 600-0051L	Rack	Technical panel Touchscreen	28,30
38	<input type="checkbox"/>	CV - Patch Panel (Option)	Sommer - 600-0051L	Rack	Technical panel Touchscreen	28,30
39	<input type="checkbox"/>	Spare 1 - W25	Sommer - 600-0051L	Rack	Technical panel Touchscreen	28,30
40	<input type="checkbox"/>	Spare 2 - W25	Sommer - 600-0051L	Rack	Technical panel Touchscreen	28,30
41	<input type="checkbox"/>	Y - Dvd Recorder Out	Sommer - 600-0051L	Rack	Medical Tower	29,50
42	<input type="checkbox"/>	C - Dvd Recorder Out	Sommer - 600-0051L	Rack	Medical Tower	29,50
43	<input type="checkbox"/>	Y - Dvd recorder In	Sommer - 600-0051L	Rack	Medical Tower	29,50
44	<input type="checkbox"/>	C - Dvd recorder In	Sommer - 600-0051L	Rack	Medical Tower	29,50
45	<input type="checkbox"/>	Y - Laparosc	Sommer - 600-0051L	Rack	Medical Tower	29,50
46	<input type="checkbox"/>	C - Laparosc	Sommer - 600-0051L	Rack	Medical Tower	29,50
47	<input type="checkbox"/>	Spare 1 - W25	Sommer - 600-0051L	Rack	Medical Tower	29,50
48	<input type="checkbox"/>	Spare 2 - W25	Sommer - 600-0051L	Rack	Medical Tower	29,50
49	<input type="checkbox"/>	AUDIO - Dvd Recorder In	Sommer - 200-0401	Rack	Medical Tower	29,50
50	<input type="checkbox"/>	AUDIO - Dvd Recorder Out	Sommer - 200-0401	Rack	Medical Tower	29,50
51	<input type="checkbox"/>	Spare 1 - W23	Sommer - 200-0401	Rack	Medical Tower	29,50
52	<input type="checkbox"/>	Spare 2 - W23	Sommer - 200-0401	Rack	Medical Tower	29,50